

Exhaust air flow control valve GRE-1/4

Part number: 10352

FESTO



 General operating condition

Data sheet

Feature	Value
Valve function	Sound pressure control function
Selection of additional functions	With silencer
Pneumatic connection, port 1	G1/4
Adjustment component	Slotted head screw
Type of mounting	Screw-in
Standard nominal flow rate in flow control direction	996 l/min
Standard flow rate 0.6->0 MPa (6->0 bar, 87->0 psi)	0 l/min ... 996 l/min
Operating pressure	0 bar ... 10 bar
Ambient temperature	-10 °C ... 70 °C
Mounting position	optional
Symbol	00991451
Operating medium	Compressed air to ISO 8573-1:2010 [7::-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	-10 °C ... 70 °C
Product weight	25 g
Material screwed plug	Wrought aluminium alloy
Note on materials	RoHS-compliant
Material seals	NBR
Material adjusting screw	Brass