

# Rod clevis SGA-M20X1,5

Part number: 10769

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	M20x1.5
Radial deviation +/-	5 mm
Angle compensation +/-	120 deg
Mounting position	Any
Threaded connection	Male thread M20x1.5
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	9 kN
Product weight	954 g
Note on materials	RoHS compliant
Material bolt	Galvanised steel
Material rod eye	Steel Galvanised
Material lock	Spring steel, galvanised