

Shock absorber DYEF-S-M5-Y1

Part number: 1152507

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	M5
Stroke	1.5 mm
Cushioning	Elastic cushioning rings/pads at both ends without metal fixed stop
Mounting position	Any
Position detection	None
Max. impact speed	0.8 m/s
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	0 °C ... 60 °C
Cushioning length	1.5 mm
Max. energy consumption per stroke	0.05 J
Product weight	2 g
Type of mounting	Via lock nut
Note on materials	RoHS compliant
Material seals	NBR
Material housing	High-alloy steel