

# Barbed bulkhead connector SCN-PK-4

Part number: 11973

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Nominal size	2.8 mm
Operating pressure complete temperature range	-0.95 bar ... 10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	0 °C ... 60 °C
Pneumatic connection, port 1	For tubing outside diameter of 6 mm
Note on materials	RoHS compliant
Material housing	Aluminium
Material nut	Galvanised steel