

Barbed bulkhead connector SCN-PK-6

Part number: 11974

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Nominal size | 4.8 mm |
| Operating pressure complete temperature range | -0.95 bar ... 10 bar |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:-:-] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | 0 °C ... 60 °C |
| Pneumatic connection, port 1 | For tubing outer diameter of 8 mm |
| Note on materials | RoHS compliant |
| Material housing | Aluminium |
| Material nut | Galvanised steel |