

Clamping module EV-15/40-4

Part number: 13289

FESTO



 General operating condition

Data sheet

| Feature | Value |
|--|---|
| Stroke | 4 mm |
| Clamping surface | 15x40 |
| Mounting position | Any |
| Mode of operation | Single-acting |
| Symbol | 00991208 |
| Operating pressure | 0.2 MPa ... 0.6 MPa |
| Operating pressure | 2 bar ... 6 bar |
| Operating pressure | 29 psi ... 87 psi |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:-:-] |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Suitability for the production of Li-ion batteries | Metals with more than 5% by mass of copper are excluded from use. Exceptions are printed circuit boards, cables, electrical connectors and coils. |
| Ambient temperature | -20 °C ... 40 °C |
| Product weight | 45 g |
| Type of mounting | With through-hole |
| Pneumatic connection | M5 |
| Material housing | Die-cast aluminium |
| Material membrane | TPE-U(PU) |