

# Blanking plug QSMC-2H

Part number: 133036

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	Mini
Mounting position	Any
Design	Blanking plug
Size of pack	10
Operating pressure complete temperature range	-0.095 MPa ... 0.6 MPa
Operating pressure complete temperature range	-0.95 bar ... 6 bar
Operating pressure complete temperature range	-13.775 psi ... 87 psi
Temperature-dependent operating pressure	-0.095 MPa ... 1.4 MPa
Temperature-dependent operating pressure	-0.95 bar ... 14 bar
Temperature-dependent operating pressure	-13.775 psi ... 203 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7::-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 80 °C
Product weight	0.1 g
Pneumatic connection, port 1	Push-in sleeve Ø 2 mm
Note on materials	RoHS compliant
Material housing	PBT