

Flow control/silencer VFFK-C-K-M7-P

Part number: 133141

FESTO



 General operating condition

Data sheet

Feature	Value
Valve function	Sound pressure control function
Selection of additional functions	With silencer
Pneumatic connection, port 1	M7
Adjustment component	Knurled screw
Type of mounting	Screw-in
Standard flow rate 0.6-10 MPa (6-10 bar, 87-10 psi)	0 l/min ... 100 l/min
Operating pressure	0 bar ... 10 bar
Ambient temperature	0 °C ... 60 °C
Type of seal on screwed plug	Sealing ring
Mounting position	Any
Symbol	00991451
Operating pressure complete temperature range	0 bar ... 10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	0 °C ... 60 °C
Nominal torque	3.8 Nm
Tolerance for nominal tightening torque	±20%
Product weight	5.8 g
Material shock absorber insert	Packaging unit
Material screwed plug	Nickel-plated brass
Note on materials	RoHS compliant
Material seals	NBR
Material adjusting screw	Nickel-plated brass