

Rod clevis CRSG-M10X1,25

Part number: 13569

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	M10x1.25
Mounting position	Any
Based on standard	ISO 8140
Threaded connection	Female thread M10x1.25
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper, zinc or nickel are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils.
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	0.9 kN
Product weight	101.8 g
Material rod clevis	High-alloy steel
Note on materials	RoHS compliant
Material bolt	High-alloy steel
Material nut	High-alloy steel
Material lock	High-alloy steel