

Plug socket MSSD-E

Part number: 14098

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Type of mounting	On solenoid valve via M3 central screw
Mounting position	Any
Product weight	8 g
Electrical connection 1	Angled socket, square design, 3-pin, type C
Electrical connection 2	Screw terminal
Operational voltage range DC	0 V ... 300 V
Operational voltage range AC	0 V ... 250 V
Current rating at 40° C	6 A
Cable fitting	Pg7
Cable diameter	6 mm ... 8 mm
Connection cross section	0.75 mm ²
Degree of protection	IP65
Ambient temperature	-25 °C ... 90 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Pollution degree	3
Material housing	Reinforced PA
Housing colour	Black
Material seals	NBR