

Multi-socket KDVF6-12

Part number: 152510

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|------------------------------------|--|
| Nominal size | 6 mm |
| Operating pressure | -0.95 bar ... 10 bar |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:-:-] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Media temperature | -10 °C ... 60 °C |
| Ambient temperature | -10 °C ... 60 °C |
| Max. number of connections | 12 |
| Pneumatic connection | PK-6 |
| Colour | Grey |
| Note on materials | RoHS compliant |