

Push-in L-fitting, rotatable QSRL-3/8-8

Part number: 153415

FESTO



 General operating condition

Data sheet

| Feature | Value |
|---|---|
| Size | Standard |
| Nominal size | 4.6 mm |
| Tubing insertion depth | 18 mm |
| Type of seal on screwed plug | Coating |
| Mounting position | Any |
| Design | L-shape |
| Size of pack | 1 |
| Design | Push-pull principle |
| Operating pressure complete temperature range | -0.095 MPa ... 0.6 MPa |
| Operating pressure complete temperature range | -0.95 bar ... 6 bar |
| Operating pressure complete temperature range | -13.775 psi ... 87 psi |
| Temperature-dependent operating pressure | -0.095 MPa ... 1.4 MPa |
| Temperature-dependent operating pressure | -0.95 bar ... 14 bar |
| Temperature-dependent operating pressure | -13.775 psi ... 203 psi |
| Max. rotational speed | 400 rpm |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:-:-] |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | 0 °C ... 60 °C |
| Max. radial torque | 0.015 Nm |
| Nominal torque | 15.5 Nm |
| Tolerance for nominal tightening torque | ±20% |
| Product weight | 39 g |
| Type of mounting | External hex SW17 |
| Pneumatic connection, port 1 | Male thread R3/8 |
| Pneumatic connection, port 2 | For tubing outside diameter of 8 mm |
| Colour of release ring | Blue |
| Material screwed plug | Nickel-plated brass |
| Note on materials | RoHS compliant |
| Material housing | PBT |
| Material release ring | POM |
| Material tubing seal | NBR |
| Material tubing clamp component | High-alloy stainless steel |