


Check valve H-QS-8

Part number: 153464

FESTO



Data sheet

 [General operating condition](#)

| Feature | Value |
|---|--|
| Valve function | With non-return function |
| Pneumatic connection, port 1 | QS-8 |
| Pneumatic connection, port 2 | QS-8 |
| Type of mounting | Inline installation |
| Standard nominal flow rate (standardised to DIN 1343) | 681 l/min |
| Operating pressure | -1 bar ... 10 bar |
| Ambient temperature | 0 °C ... 60 °C |
| Material housing | Anodised aluminium |
| Housing colour | Black |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:-:-] |
| Symbol | 00991455 |
| Min. diff. pressure, opening | 0.1 bar |
| Min. diff. pressure, closing | 0.2 bar |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Product weight | 21 g |
| Note on materials | RoHS compliant |