

Barbed hose fitting N-1/4-P-9-MS

Part number: 15632

FESTO



 General operating condition

Data sheet

Feature	Value
Nominal size	6.5 mm
Type of seal on screwed plug	Sealing ring
Mounting position	Any
Design	Straight design
Size of pack	10
Operating pressure complete temperature range	-0.95 bar ... 16 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7::-:]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Max. tightening torque	12 Nm
Product weight	21.92 g
Pneumatic connection, port 1	Male thread G1/4
Pneumatic connection, port 2	For tubing inside diameter of 9 mm
Note on materials	RoHS compliant
Material housing	Brass