

Sensor bracket DASI-Q11-25-A-SR

Part number: 1568451

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	25
Design	For T-slot
For piston diameter	Ø25
Design	Sensor rail
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Product weight	32 g
Type of mounting	Clamped in T-slot Via through-hole and screw With slot nuts
Note on materials	RoHS compliant
Material screws	Steel Galvanised