

Swivel flange SNGB-250

Part number: 157512

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	250
Based on standard	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C ... 90 °C
Product weight	16141 g
Note on materials	RoHS compliant
Material mounting	Spheroidal graphite cast iron
Material bolt	Steel Galvanised
Material bearing	Polymer
Material disc	Galvanised steel
Material screws	Steel Galvanised
Material lock	Spring steel, galvanised