

# Clevis foot CRLNG-50

Part number: 161842

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	50
Based on standard	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Mounting position	Any
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Ambient temperature	-40 °C ... 80 °C
Max. load capacity	2.5 kN
Product weight	281 g
Note on materials	RoHS compliant
Material mounting	Electropolished High-alloy steel
Material bearing	Polymer