

Trunnion flange CRZNG-63

Part number: 161855

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	63
Based on standard	ISO 15552
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper, zinc or nickel are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils.
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	4 kN
Product weight	687 g
Note on materials	RoHS compliant
Material mounting	High-alloy stainless steel
Material screws	High-alloy stainless steel