

Short-stroke cylinder ADVC-4-5-A-P

Part number: 188055

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Stroke	5 mm
Piston diameter	4 mm
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	Any
Mode of operation	Double-acting
Design	Piston Piston rod
Position detection	None
Symbol	00991227
Operating pressure	0.2 MPa ... 0.8 MPa
Operating pressure	2 bar ... 8 bar
Operating pressure	29 psi ... 116 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C ... 80 °C
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	5.7 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	7.5 N
Moving mass	0.25 g
Product weight	4.3 g
Type of mounting	With through-hole With accessories
Pneumatic connection	M3
Note on materials	RoHS compliant
Material cover	Wrought aluminium alloy anodised
Material seals	HNBR NBR
Material housing	anodised
Material piston rod	Wrought aluminium alloy anodised