

Holder for suction cup with connection ESH-HA-1-PK

Part number: 189194

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|-----------------------------------|---|
| Nominal size | 2.5 mm |
| Volume | 0.09 cm ³ |
| Mounting position | Any |
| Design | Vacuum port on top |
| Correlation to suction-cup holder | Size 1 |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7::-] |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-A1-L |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 3 g |
| Type of mounting | Via lock nut |
| Suction cup mounting | Diameter 3 mm |
| Vacuum connection | PK-3 |
| Note on materials | RoHS compliant |
| Material seals | NBR Steel |
| Material retaining bracket | Tempered steel High-alloy steel |