

# Holder for suction cup with connection ESH-HA-5-G

Part number: 189201

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Nominal size	8 mm
Volume	1.862 cm <sup>3</sup>
Mounting position	Any
Design	Vacuum port on top
Correlation to suction-cup holder	Size 5
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-10 °C ... 60 °C
Product weight	84 g
Type of mounting	Via lock nut
Suction cup mounting	M10
Vacuum connection	G1/8
Note on materials	RoHS compliant
Material retaining bracket	Tempered steel High-alloy steel