

Holder for suction cup with connection ESH-HB-3-QS

Part number: 189207

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal size	3.3 mm
Volume	0.519 cm ³
Mounting position	Any
Design	Vacuum port on side
Correlation to suction-cup holder	Size 3
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	0 °C ... 60 °C
Product weight	29 g
Type of mounting	With female thread
Suction cup mounting	M4
Vacuum connection	QS-6
Note on materials	RoHS compliant
Material seals	NBR Steel
Material retaining bracket	Tempered steel High-alloy steel