

Holder for suction cup with connection ESH-HC-2-PK

Part number: 189216

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Height compensator for suction-cup holder	3 mm
Nominal size	1.2 mm
Volume	0.192 cm ³
Mounting position	Vertical
Design	Vacuum port on top With height compensator
Correlation to suction-cup holder	Size 2
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-10 °C ... 60 °C
Product weight	8 g
Type of mounting	Via lock nut
Suction cup mounting	Diameter 4 mm
Vacuum connection	PK-4
Note on materials	RoHS compliant
Material seals	NBR Steel
Material retaining bracket	Tempered steel High-alloy steel