

Holder for suction cup with connection ESH-HCL-6-G

FESTO

Part number: 189232



 [General operating condition](#)

Data sheet

| Feature | Value |
|-------------------------------------------|-------------------------------------------------|
| Height compensator for suction-cup holder | 40 mm |
| Nominal size | 10 mm |
| Volume | 16.325 cm ³ |
| Mounting position | Vertical |
| Design | Vacuum port on top With height compensator |
| Correlation to suction-cup holder | Size 6 |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7::-] |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-A1-L |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 560 g |
| Type of mounting | Via lock nut |
| Suction cup mounting | M20x2 |
| Vacuum connection | G1/4 |
| Note on materials | RoHS compliant |
| Material retaining bracket | Tempered steel High-alloy steel |