

# Holder for suction cup with connection ESH-HDL-1-PK

Part number: 189244

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Height compensator for suction-cup holder	10 mm
Nominal size	1.9 mm
Volume	0.15 cm <sup>3</sup>
Mounting position	Vertical
Design	Vacuum port on side With height compensator
Correlation to suction-cup holder	Size 1
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-10 °C ... 60 °C
Product weight	28 g
Type of mounting	Via lock nut
Suction cup mounting	Diameter 3 mm
Vacuum connection	PK-3
Note on materials	RoHS compliant
Material seals	NBR Steel
Material retaining bracket	Tempered steel High-alloy steel