

Holder for suction cup with connection ESH-HDL-5-G

FESTO

Part number: 189251



 [General operating condition](#)

Data sheet

Feature	Value
Height compensator for suction-cup holder	30 mm
Nominal size	8.5 mm
Volume	1.667 cm ³
Mounting position	Vertical
Design	Vacuum port on side With height compensator
Correlation to suction-cup holder	Size 5
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-10 °C ... 60 °C
Product weight	273 g
Type of mounting	Via lock nut
Suction cup mounting	M10
Vacuum connection	G1/8
Note on materials	RoHS compliant
Material retaining bracket	Tempered steel High-alloy steel