

# Holder for suction cup with connection ESH-HE-5-G1/4

Part number: 189257

FESTO



 [General operating condition](#)

## Data sheet

| Feature                           | Value   |
|-----------------------------------|---|
| Nominal size                      | 7 mm  |
| Volume                            | 1.227 cm <sup>3</sup>                           |
| Mounting position                 | Any   |
| Design                            | Vacuum port on top                              |
| Correlation to suction-cup holder | Size 5  |
| Operating medium                  | Atmospheric air based on ISO 8573-1:2010 [7::-] |
| Corrosion resistance class CRC    | 1 - Low corrosion stress                        |
| LABS (PWIS) conformity            | VDMA24364-A1-L                                  |
| Ambient temperature               | -10 °C ... 60 °C                                |
| Product weight                    | 24 g  |
| Type of mounting                  | With male thread<br>Via vacuum port             |
| Suction cup mounting              | M10   |
| Vacuum connection                 | G1/4  |
| Note on materials                 | RoHS compliant                                  |
| Material seals                    | Wrought aluminium alloy<br>NBR<br>POM<br>Steel  |
| Material retaining bracket        | Tempered steel                                  |