

Holder for suction cup with connection ESH-HF-3-M14X1

Part number: 189262

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Height compensator for suction-cup holder	6 mm
Nominal size	3.3 mm
Volume	0.4 cm ³
Mounting position	Vertical
Design	Vacuum port on top With height compensator
Correlation to suction-cup holder	Size 3
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-10 °C ... 60 °C
Product weight	54 g
Type of mounting	With male thread Via vacuum port
Suction cup mounting	M4
Vacuum connection	M14x1
Note on materials	RoHS compliant
Material seals	NBR POM
Material retaining bracket	Tempered steel