

Suction cup with connection ESS-2-SN

Part number: 189264

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Min. workpiece radius	10 mm
Nominal size	0.6 mm
Suction cup diameter	2 mm
Suction cup volume	0.002 cm ³
Suitable for ejector pulse	≤4 bar
Position of connection	On top
Mounting position	Any
Symbol	00991485
Correlation to suction-cup holder	Size 1
Suction cup shape	Round, flat
Operating pressure	-0.095 MPa ... 0 MPa
Operating pressure	-0.95 bar ... 0 bar
Operating pressure	-13.775 psi ... 0 psi
Nominal operating pressure	-0.07 MPa
Nominal operating pressure	-0.7 bar
Nominal operating pressure	-10.15 psi
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Suitable for use with food	See supplementary material information
Ambient temperature	-10 °C ... 70 °C
Holding force at nominal operating pressure	0.1 N
Lateral force at nominal operating pressure	0.5 N
Product weight	0.1 g
Type of mounting	Via vacuum port
Vacuum connection	Outside diameter 3 mm
Colour	Black
Shore hardness	50 +/-5
Material screwed plug	Nickel-plated brass
Note on materials	RoHS compliant
Material suction cup	NBR