

# Barbed fitting CN-M5-PK-2

Part number: 19521

FESTO



 [General operating condition](#)

## Data sheet

| Feature                                       | Value  |
|---|--|
| Nominal size                                  | 1.5 mm   |
| Type of seal on screwed plug                  | Sealing ring   |
| Operating pressure complete temperature range | -0.95 bar ... 10 bar   |
| Operating medium                              | Compressed air to ISO 8573-1:2010 [7::-]   |
| Note on operating and pilot medium            | Lubricated operation possible (in which case lubricated operation will always be required) |
| LABS (PWIS) conformity                        | VDMA24364-B1/B2-L  |
| Ambient temperature                           | 0 °C ... 60 °C   |
| Pneumatic connection, port 1                  | Male thread M5   |
| Pneumatic connection, port 2                  | For tubing outer diameter of 3 mm  |
| Note on materials                             | RoHS compliant   |
| Material housing                              | Steel  |