

Rotary distributor GF-1/4

Part number: 2094

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal size	11.5 mm
Mounting position	Any
Operating pressure complete temperature range	-0.095 MPa ... 1 MPa
Operating pressure complete temperature range	-0.95 bar ... 10 bar
Operating pressure complete temperature range	-13.775 psi ... 145 psi
Standard flow rate 1-2.1 (6->0)	2932 l/min
Standard flow rate 1-2.X open (6->0)	2977 l/min
Standard nominal flow rate 1.1-2.1	1792 l/min
Max. rotational speed	300 rpm
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Product weight	250 g
Pneumatic connection, port 1	Male thread G1/4
Pneumatic connection, port 2	Female thread G1/4
Note on materials	RoHS compliant
Material housing	Wrought aluminium alloy
Material shaft	High-alloy steel