

# Quick coupling plug KS4-N-9

Part number: 2153

FESTO



 General operating condition

## Data sheet

Feature	Value
Nominal size	7 mm
Operating pressure complete temperature range	-0.095 MPa ... 1.2 MPa
Operating pressure complete temperature range	-0.95 bar ... 12 bar
Operating pressure complete temperature range	-13.775 psi ... 174 psi
Standard nominal flow rate (standardised to DIN 1343)	711 l/min ... 1134 l/min
Nominal flow rate standardised according to ISO 8778	770.7 l/min ... 1229.3 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7::-:]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Product weight	18 g
Pneumatic connection, port 1	Barbed hose fitting 9 mm
Note on materials	RoHS compliant
Information on materials	Brass, nickel-plated