

Connecting cable

NEBV-C-S1WA25HS-K-2.5-N-LE25-S10

FESTO

Part number: 2265131



 General operating condition

Data sheet

Feature	Value
Based on standard	DIN 47100
Cable designation	Without inscription label holder
Frequency of connection	50
Product weight	460 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	Square
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connector system	Sub-D
Electrical connection 1, number of connections/cores	25
Electrical connection 1, used connections/cores	25
Electrical connection 1, type of mounting	2x screw 4-40 UNC With seal
Electrical connection 1, connection pattern	00995642
Electrical connection 2, function	Control side
Electrical connection 2, connection type	Cable
Electrical connection 2, connector system	Open end
Electrical connection 2, number of connections/cores	25
Operational voltage range DC	0 V ... 30 V
Current rating at 40° C	2.6 A
Protective conductor connection	Not provided
Cable length	2.5 m
Cable characteristic	Standard
Bending radius, fixed cable	≥41 mm
Bending radius, moving cable	≥122 mm
Cable diameter	10.2 mm
Cable diameter tolerance	± 0.25 mm
Cable structure	25 x 0.34 mm ²
Nominal cross section conductor	0.34 mm ²
Degree of protection	IP65 IP67 IP69K
Note on degree of protection	In mounted state
Special characteristics	Easy to clean
Ambient temperature	-5 °C ... 60 °C
Ambient temperature with moving cable	-5 °C ... 60 °C

Feature	Value
Storage temperature	-20 °C ... 40 °C
CE mark (see declaration of conformity)	In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS compliant
Pollution degree	3
Note on the contamination level	In mounted state
Corrosion resistance class CRC	3 - high corrosion stress
Material cable sheath	PVC
Cable sheath colour	Grey
Material housing	Reinforced PA
Housing colour	Grey
Material screws	Stainless steel
Material seals	EPDM
Material electrical contact	Gold-plated bronze
Material insulating sheath	PVC