


# Shock absorber DYSC-25-25-Y1F

Part number: 2480234

FESTO



[PDF](#) General operating condition

## Data sheet

Feature	Value
Size	25
Stroke	25 mm
Cushioning	Self-adjusting
Mounting position	Any
Position detection	None
Symbol	00991497
Max. impact speed	3 m/s
Reset time at room temperature	0.3 s
Reset time at min. ambient temperature	1 s
Mode of operation	Pushing Single-acting
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C ... 80 °C
Cushioning length	25 mm
Max. stop force	4000 N
Max. energy consumption per stroke	100 J
Max. energy consumption per hour	140000 J
Max. residual energy	0.8 J
Reset force	14 N
Min. insertion force	140 N
Product weight	575 g
Load range	160 kg
Type of mounting	Via lock nut
Note on materials	RoHS compliant
Material seals	NBR
Material housing	Galvanised steel
Material piston rod	High-alloy steel