

Clevis foot LSNG-63

Part number: 31743

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	63
Based on standard	VDMA 24562
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	4 kN
Product weight	534 g
Note on materials	RoHS compliant
Material mounting	Spheroidal graphite cast iron
Material rod end bearing	Steel PTFE