

# Clevis foot LSNSG-100

Part number: 31752

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	100
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	9 kN
Product weight	830 g
Note on materials	RoHS compliant
Material mounting	Steel Galvanised
Material rod end bearing	Steel PTFE