

Clevis foot LNG-32

Part number: 33890

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	32
Based on standard	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C ... 80 °C
Max. load capacity	0.9 kN
Product weight	133 g
Note on materials	RoHS compliant
Material mounting	Tempered steel
Material bearing	Process automation