

Swivel flange SNGB-160

Part number: 34547

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	160
Based on standard	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C ... 90 °C
Product weight	3445 g
Note on materials	RoHS compliant
Material mounting	Die-cast aluminium
Material bolt	Steel Galvanised
Material bearing	Polymer
Material disc	Galvanised steel
Material screws	Steel Galvanised
Material lock	Spring steel, galvanised