

Barbed elbow fitting LCNH-1/8-PK-6

Part number: 35987

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Nominal size | 4.9 mm |
| Type of seal on screwed plug | Sealing ring |
| Operating pressure complete temperature range | -0.95 bar ... 10 bar |
| Operating medium | Compressed air to ISO 8573-1:2010 [7::-] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | 0 °C ... 60 °C |
| Pneumatic connection, port 1 | Male thread G1/8 |
| Pneumatic connection, port 2 | For tubing outside diameter of 8 mm |
| Note on materials | RoHS compliant |
| Material housing | Aluminium Die-cast zinc |