

Coupling piece KSZ-M12X1,25

Part number: 36126

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|---|
| Size | M12x1.25 |
| Mounting position | Any |
| Threaded connection | Female thread M12x1.25 |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Suitability for the production of Li-ion batteries | Metals with more than 1% by mass of copper are excluded from use. Exceptions are printed circuit boards, cables, electrical connectors and coils. |
| Ambient temperature | -40 °C ... 150 °C |
| Max. load capacity | 1.5 kN |
| Product weight | 180 g |
| Note on materials | RoHS compliant |
| Material mounting | Steel Galvanised |
| Material thread piece | Steel Galvanised |