

# Sealing ring OK-3/8

Part number: 531773

FESTO



 [General operating condition](#)

## Data sheet

| Feature                                       | Value  |
|---|--|
| Based on standard                             | ISO 16030  |
| Operating pressure complete temperature range | -0.095 MPa ... 1 MPa   |
| Operating pressure complete temperature range | -0.95 bar ... 10 bar   |
| Operating pressure complete temperature range | -13.775 psi ... 145 psi  |
| Operating medium                              | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Note on operating and pilot medium            | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC                | 2 - Moderate corrosion stress  |
| LABS (PWIS) conformity                        | VDMA24364-B2-L   |
| Ambient temperature                           | -10 °C ... 60 °C   |
| Tightening by hand at room temperature        | Yes  |
| Nominal torque                                | 12.5 Nm  |
| Tolerance for nominal tightening torque       | ±20%   |
| Product weight                                | 0.44 g   |
| Pneumatic connection                          | G3/8   |
| Note on materials                             | RoHS compliant   |
| Material stops                                | Reinforced PA  |
| Material seals                                | TPE-U(PU)  |