

Sub-base-SET MS12-AGG

Part number: 537136

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	12
Series	MS
Mounting position	Any
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C ... 60 °C
Media temperature	-10 °C ... 60 °C
Product weight	1300 g
Pneumatic connection, port 1	G1 1/4
Pneumatic connection, port 2	G1 1/4
Note on materials	RoHS compliant
Material sub-base	Die-cast aluminium
Material seals	NBR