

# Shock absorber YSRW-DGC-12

Part number: 540345

FESTO



[PDF](#) [General operating condition](#)

## Data sheet

Feature	Value
Size	12
Cushioning	Self-adjusting Soft characteristic curve
Mounting position	Any
Position detection	None
Symbol	00991497
Max. impact speed	2 m/s
Mode of operation	Pushing Single-acting
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 80 °C
Type of mounting	Via lock nut
Note on materials	RoHS compliant
Material piston rod	High-alloy steel