

Ball valve actuator unit VZPR-BPD-22-R112

Part number: 540516

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Design	Semi-rotary drive
Type of actuation	Electric Pneumatic
Mounting position	optional
Type of mounting	Via female thread
Connection Process valve	Rp1 1/2
Switching position indicator	Knob actuator direction = flow direction
Nominal size DN	40
Operating pressure of ball valve drive unit	1 bar ... 8.4 bar
Nominal pressure PN	25
Symbol	00991921
Media temperature	-20 °C ... 150 °C
Ambient temperature	-20 °C ... 80 °C
LABS (PWIS) conformity	VDMA24364 zone III
Product weight	3800 g
Corrosion resistance class CRC	1 - Low corrosion stress