

On/off valve MS4-EM1-1/8

Part number: 541262

FESTO



 General operating condition

Data sheet

Feature	Value
Design	Rotary switching valve
Type of actuation	Manual
Exhaust-air function	Cannot be throttled
Type of piloting	Direct
Symbol	00991670
Valve function	3/2-way, double solenoid
Operating pressure	0 MPa ... 1.4 MPa
Operating pressure	0 bar ... 14 bar
C value	4.6 l/sbar
b value	0.51
Standard nominal flow rate (standardised to DIN 1343)	1200 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4] Inert gas
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
Note on materials	RoHS compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Suitable for use with food	See supplementary material information
Type of mounting	Either: Inline installation With accessories
Mounting position	Any
Flow direction	Non-reversible
Product weight	190 g
Pneumatic connection, port 1	G1/8
Pneumatic connection, port 2	G1/8
Pneumatic connection, port 3	G1/4
Material seals	TPE-U(PU)
Material housing	Die-cast aluminium