

Branching module MS12-FRM-G

Part number: 541681

FESTO



 General operating condition

Data sheet

Feature	Value
Mounting position	Any
Design	Branching module
Symbol	00991510
Operating pressure	0 bar ... 20 bar
Standard nominal flow rate in main flow direction 1->2	25000 l/min ... 42000 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [-::-]
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C ... 60 °C
Media temperature	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Product weight	3000 g
Type of mounting	Inline installation With accessories
Pneumatic connection, port 1	Manifold module
Pneumatic connection, port 2	Manifold module
Pneumatic connection, port 3	G2
Pneumatic connection, port 4	G1
Material sub-base	Die-cast aluminium
Material mounting bracket	Die-cast aluminium
Material seals	NBR
Material housing	Die-cast aluminium
Material module connector	Die-cast aluminium