

Connecting component KVI-CP-3-SSD

Part number: 543252

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Type of mounting	With male thread
Product weight	48 g
Electrical connection	M9 Plug
Operational voltage range DC	60 V
Degree of protection	IP65 IP67
Ambient temperature	-20 °C ... 80 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Corrosion resistance class CRC	2 - Moderate corrosion stress
Material housing	nickel-plated
Material seals	NBR
Mounting position	Any