

# Branching module MS4-A-IPM-80

Part number: 543498

FESTO



 [General operating condition](#)

## Data sheet

| Feature                        | Value                         |
|--------------------------------|-------------------------------|
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity         | VDMA24364-B1/B2-L             |
| Media temperature              | -10 °C ... 60 °C              |
| Product weight                 | 124 g                         |
| Note on materials              | RoHS compliant                |
| Material sub-base              | Die-cast aluminium            |
| Material seals                 | NBR                           |
| Material hollow bolt           | Die-cast aluminium            |
| Material module connector      | Die-cast aluminium            |
| Material screws                | Steel                         |