

Solenoid coil MH-2-24VDC-PA

Part number: 549906

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting position	Any
Switching position indicator	No
Min. pick-up time	12 ms
Duty cycle	100%
Power factor (cos phi)	0.7
Characteristic coil data	24 V DC: 7.9 W
Permissible frequency fluctuations	+/-10%
Permissible voltage fluctuations	+/-10%
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP65
Note on degree of protection	IP00 without connector socket
Ambient temperature	-20 °C ... 50 °C
Max. tightening torque for fitting	2 Nm
Product weight	150 g
Electrical connection	To DIN EN 175301-803
Type of mounting	Via lock nut
Material solenoid coil	Duroplast Copper Steel
Material winding	Copper