


Electrical sub-base VAVE-L1-1VS3-LP

Part number: 566719

FESTO



Data sheet

 [General operating condition](#)

Feature	Value
Reverse polarity protection	Bipolar
Additional functions	Spark arresting
Signal status display	LED
Nominal operating voltage DC	12 V
Immunity to surge	0.8 kV
Pollution degree	3
Extended ambient temperature	-5 - 60 °C
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP40
Ambient temperature	-5 °C ... 50 °C
Mounting position	Any
Product weight	1.6 g
Electrical connection	2-pin Socket
Protective conductor connection	Not provided
Type of mounting	Clip
Housing colour	Black
Note on materials	RoHS compliant
Material housing	Process automation